

LPTE14-750SS

by CMC

Catalog ID: LPTE14-750SS



Pad mounted termination enclosures, Three-Phase, NEMA 3R (rain-proof), 600 Volt Rated, Stainless steel cabinets

- Aluminum mechanical bar connector eliminates compression tools, lugs and bolt assemblies
- Aluminum enclosure is lightweight, low maintenance and has excellent corrosion resistance
- Ample working space, allowing for easier termination with a removable swinging door
- All-welded construction: welds and seams are ground smooth
- Manufactured to meet or exceed ANSI C57-12.28 for wall-mount equipment enclosure integrity
- Removable swinging doors - Doors have stainless steel lift off hinges with stainless steel three-point locking handles and recessed stainless steel penta-head bolts for security
- Finish is Munsell green, oven cured powder coat
- All mounting hardware is 18-8 stainless steel
- Any pad mount enclosure can be made with a lift-off (removable) top. In order to designate this use "LPLE" instead of "LPTE"

Product Details

General

Material	Aluminum
----------	----------

Dimensions

Depth	24 in
Height	44 in
Width	25 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	750 Kcmil - #2 AWG
Number Of Conductors	14



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

