

# LPTE18-750LI

by CMC

Catalog ID: LPTE18-750LI



Three-Phase, NEMA 3R (rain-proof), 600 Volt Rated pad-mounted termination enclosures

- Aluminum enclosure is lightweight, low maintenance and has excellent corrosion resistance
- All-welded construction: Welds and seams are ground smooth.
- Removable swinging doors - Doors have stainless steel lift off hinges with stainless steel threepoint locking handles and recessed stainless steel penta-head bolts for security
- Finish is Munsell green, oven cured powder coat
- All mounting hardware is 18-8 stainless steel.
- Aluminum mechanical bar connector eliminates compression tools, lugs and bolt assemblies
- Unique lay-in feature reduces frustration of feeding multiple conductors through standard connectors
- Each outlet has a removable “keeper” that allows conductors to be laid into the outlet, solving the problem of trying to bend large conductors in confined areas. The “keeper” is then slid over the conductor and the set-screws are tightened. It is fast and easy at initial installations and for later service additions.
- Connectors are fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Fully tested to ANSI C119.4 for Class “A” connectors.
- Any pad mount enclosure can be made with a lift-off (removable) top. In order to designate this use “LPLE” instead of “LPTE”

Rain Proof

## Product Details

### General

Type	LPTE/LPLE - LI
------	----------------

### Dimensions

Dimensions	36 in x 30 in x 44 in
------------	-----------------------

Height	44 in
Length	36 in
Width	30 in

### Electrical Ratings

Phase	3-Phase
Voltage Rating	600 V

### Conductor Related

Conductor Range	750 Kcmil - #2 AWG
Number Of Conductors	18

### Certifications and Compliance

Nema Rating	3R
-------------	----



**CONNECTOR MANUFACTURING COMPANY**  
3501 Symmes Road  
Hamilton, Ohio 45015 - 1369  
513 - 860 - 4455(Press 2 for Customer Service and Sales)  
To email customer Service: [jrex@cmclugs.com](mailto:jrex@cmclugs.com)

