

LPTE30-1000SS

by CMC

Catalog ID: LPTE30-1000SS

Pad mounted termination enclosures, Three-Phase, NEMA 3R (rain-proof), 600 Volt Rated, Stainless steel cabinets

- Aluminum mechanical bar connector eliminates compression tools, lugs and bolt assemblies
- Aluminum enclosure is lightweight, low maintenance and has excellent corrosion resistance
- Ample working space, allowing for easier termination with a removable swinging door
- All-welded construction: welds and seams are ground smooth
- Manufactured to meet or exceed ANSI C57-12.28 for wall-mount equipment enclosure integrity
- Removable swinging doors - Doors have stainless steel lift off hinges with stainless steel three-point locking handles and recessed stainless steel penta-head bolts for security
- Finish is Munsell green, oven cured powder coat
- All mounting hardware is 18-8 stainless steel
- Any pad mount enclosure can be made with a lift-off (removable) top. In order to designate this use "LPLE" instead of "LPTE"



Product Details

General

Material	Aluminum
UPC	192663110810

Dimensions

Depth	52 in
Height	44 in
Width	54 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	1000 Kcmil-#1/0 AWG
Number Of Conductors	30