0.4 A, Type Slo-Fast Fuselinks, 23" Length, Solid Head

by CHANCE Utility
Catalog ID: M0D4SF23

0.4 amp, Type SloFast Cutout fuselink with a 23" (584.2mm) pigtail.

Product Details

General

Fuse Head Style	Solid
Fuselink Type	Type SloFast
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359042112

Dimensions

Length - Fuselink	23" (584.2mm)
Weight	0.118 lb

Electrical Ratings

Amperage Rating	0.4 A

Logistics

Pallet Quantity	4800 EA
Standard Package	10

For further technical assistance, please contact us

Domestic Customer Service
Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service
Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com