



# 32.0 A, Type Slo-Fast Fuselinks, 26" Length, Solid Head

by CHANCE Utility  
Catalog ID: M32SF

32.0 amp, Type SloFast Cutout fuselink with a 26" (660.4mm) pigtail.



## Product Details

### General

Fuse Head Style	Solid
Fuselink Type	Type SloFast
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359046998

### Dimensions

Length - Fuselink	26" (660.4mm)
Weight	0.118 lb

### Electrical Ratings

Amperage Rating	32.0 A
-----------------	--------

### Logistics

Pallet Quantity	4800 EA
Standard Package	10

For further technical assistance, please contact us

#### Domestic Customer Service

Hubbell Power Systems  
210 N. Allen Centralia, MO 65240 USA  
Phone: (573) 682-5521  
Fax: (573) 682-8475  
Email: [hpscsc@hubbell.com](mailto:hpscsc@hubbell.com)

#### International Customer Service

Phone: +1-573-682-5521  
Fax: +1-573-682-8516  
Email: [hpsintlcs@hubbell.com](mailto:hpsintlcs@hubbell.com)