



7.8 A, Type Slo-Fast Fuselinks, 23" Length, Removable Head

by CHANCE Utility
Catalog ID: M7D8SFA23

7.8 amp, Type SloFast Cutout fuselink with a 23" (584.2mm) pigtail and a removable buttonhead.



Product Details

General

Fuse Head Style	Removable
Fuselink Type	Type SloFast
Required Cutout Fuseholder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359049227

Dimensions

Length - Fuselink	23" (584.2mm)
Weight	0.127 lb

Electrical Ratings

Amperage Rating	7.8 A
-----------------	-------

Logistics

Pallet Quantity	4800 EA
Standard Package	10

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsh@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com