

## **CRT-3 - Current Transformer - Revenue Metering CT - Indoor/Outdoor - Standard Accuracy 0.3 Class**

By Meramec

CRT- 3- Indoor/Outdoor Revenue Metering Current Transformer

### **Features**

- +/- 0.3% accuracy from Nameplate Rating to Rating Factor
- +/- 0.6% accuracy from below Nameplate Rating to 5% Nameplate Rating
- Indoor/Outdoor application
- 5.5" (140 mm) window
- 8.25" (210 mm) W x 9.84" (250mm) H x 2.88" (73 mm) D
- 200A - 4000A primary current
- 5A secondary current
- 60 Hz rated frequency
- 0.6kV, 10kV BIL full wave
- 180 x Rated Current mechanical rating
- 80 x Rated Current thermal rating
- IEC version also available
- Single ratio and dual ratio available



\*Representative Image

- Optional accessories available

### **Application**

Metering

### **General**

Color - Housing                      Black

### **Product Assets**

[Sales Drawings - CRT-3](#)

[Specifications - CRT-3 - Current Transformer - Revenue Metering CT - Indoor/Outdoor - Standard Accuracy 0.3 Class](#)

[Video - Meramec Factory Tour: Cuba, MO - Hubbell Power Systems](#)