

CRT-15 - Current Transformer - Revenue Metering CT - Indoor/Outdoor - High Accuracy 0.15 Class

By Meramec

CRT- 15- Indoor/Outdoor Revenue Metering Current Transformer

Features

- +/- 0.15% accuracy from Nameplate Rating to Rating Factor
- +/- 0.3% accuracy from below Nameplate Rating to 10% Nameplate Rating
- Indoor/Outdoor application
- 5.5" (140 mm) window
- 8.25" (210 mm) W x 9.84" (250mm) H x 2.88" (73 mm) D
- 200A - 4000A primary current
- 5A secondary current
- 60 Hz rated frequency
- 0.6kV, 10kV BIL full wave
- 180 x Rated Current mechanical rating
- 80 x Rated Current thermal rating
- IEC version also available
- Single ratio and dual ratio available



- Optional accessories available

Application

Metering

General

Color - Housing Black

Product Assets

[Sales Drawings - CRT-15](#)

[Specifications - CRT-15 - Current Transformer - Revenue Metering CT - Indoor/Outdoor - High Accuracy 0.15 Class](#)

[Video - Meramec Factory Tour: Cuba, MO - Hubbell Power Systems](#)