

**CRT-15S - Current Transformer -  
Revenue Metering CT -  
Indoor/Outdoor - Special Accuracy  
0.15S Class**

By Meramec

CRT- 15S- Indoor/Outdoor Revenue Metering Current Transformer

## Features

- +/- 0.15% accuracy from 5% Nameplate Rating to Rating Factor
- Indoor/Outdoor application
- 5.5" (140 mm) window
- 8.25" (210 mm) W x 9.84" (250mm) H x 2.88" (73 mm) D
- 200A - 4000A primary current
- 5A secondary current
- 60 Hz rated frequency
- 0.6kV, 10kV BIL full wave
- 180 x Rated Current mechanical rating
- 80 x Rated Current thermal rating
- IEC version also available
- Single ratio and dual ratio available



- Optional accessories available

## Application

## Metering

## General

Color - Housing Black

## Product Assets

## Sales Drawings - CRT-15S

Specifications - CRT-15S - Current Transformer - Revenue  
Metering CT - Indoor/Outdoor - Special Accuracy 0.15S Class  
Video - Meramec Factory Tour: Cuba, MO - Hubbell Power  
Systems