



MP450 Autotransformer Closed Transition Start

By Metron/Metron-Eledyne
Catalog # HCMP450

MP450 Autotransformer Closed Transition Start



General

| | |
|-------------------|---|
| Application | Fire Protection System |
| Series | MP |
| Temperature Range | 4.4°C to 50°C |
| Type | Autotransformer Closed Transition Start |

Electrical Ratings

| | |
|------------------|-----------|
| Frequency Rating | 50/60 Hz |
| Power Factor | 15-600 |
| Voltage Rating | 200-600 V |

Certifications And Compliance

| | |
|----------------------|-----------|
| Industry Standard(s) | UL Listed |
|----------------------|-----------|

Product Assets

- [Brochures - Series MP450 Combined Manual and Automatic](#)
- [Customer Use Drawings - METRON_MP450 Schematic Drawing Pg 1](#)
- [Customer Use Drawings - METRON_MP450 Schematic Drawing Pg 2](#)
- [Installation Manuals - Manual for MP300 - MP700 - Doc605](#)
- [Submittal Packages - MP450 Submittal Selection Table](#)