



MP700 Solid State Soft Start

By Metron/Metron-Eledyne
Catalog # [HCMP700](#)

MP700 Solid State Soft Start



General

Application	Fire Protection System
Series	MP
Temperature Range	4.4°C to 50°C
Type	Solid State Soft Start

Electrical Ratings

Frequency Rating	50/60 Hz
Power Factor	15-600
Voltage Rating	200-600 V

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Product Assets

- [Brochures - Soft Start Series MP700](#)
- [Installation Manuals - Manual for MP300 - MP700 - Doc605](#)
- [Submittal Packages - MP700 Submittal Selection Table](#)