



# HCMP800TS-700 - Variable Speed Pressure Limiting Soft Start Bypass with Automatic Transfer Switch

By Metron/Metron-Eledyne  
Catalog # [HCMP800TS-700](#)

Variable Speed Pressure Limiting Soft Start Bypass with Automatic Transfer Switch

### Features

Service Entrance Rated

### Application

Fire Protection System

### General

Catalog Number	HCMP800TS-700
Series	MP
Temperature Range	4.4°C to 50°C
Type	Variable Speed Pressure Limiting with ATS



### Electrical Ratings

Frequency Rating	50/60 Hz
Power Factor	50-350
Voltage Rating	200-600 V

### Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

### Product Assets

- [Brochures - SERIES MP800 VFD](#)
- [Installation Manuals - METRON\\_MP800\\_Manual](#)
- [Specifications - HCMP800TS700](#)
- [Submittal Packages - MP800-700TS Submittal Selection Table](#)



A Hubbell brand