



## N1C243006LP

by Wiegmann  
Catalog ID: N1C243006LP

N1 Hinged-Cover 24X30X6 Carbon Steel - Gray

N1C SERIES - 14 GAUGE CARBON STEEL NEMA 1 MEDIUM HINGED WALL-MOUNT -ENCLOSURE SIZE 30.00 IN X 24.00 IN X 6.63 IN.

- Bodies and doors fabricated from 14 gauge steel. Mounting holes on back of cabinet. Collar studs provided for mounting optional back panel. Doors furnished standard with flushmount quarter-turn style latch. Doors secured by butt hinges. Grounding provisions provided.

## Product Details

### General

Application	Designed for use in control and instrumentation applications in areas which do not require oil-tight and dust-tight specifications.
Color	Gray
Construction	Seam and Spot Welded
Cover Type	Hinged Cover
Finish Type	Smooth
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Holes
Type	Enclosure
UPC	786725843947

### Dimensions

Actual Depth	6.630 in
Depth	6 in
Height	30 in
Weight	53 lb
Width	24 in

### Certifications and Compliance

Certified Listed	<ul style="list-style-type: none"><li>• UL</li><li>• CSA</li></ul>
Nema Rating	NEMA 1
UL Listed	Yes