



N1C303606LP

by Wiegmann
Catalog ID: N1C303606LP

N1 Hinged-Cover 30X36X6 Carbon Steel - Gray

Designed for use in control and instrumentation applications in areas which do not require oil-tight and dust-tight specifications.

- Bodies and doors fabricated from 14 gauge steel. Mounting holes on back of cabinet. Collar studs provided for mounting optional back panel. Doors furnished standard with flushmount quarter-turn style latch. Doors secured by butt hinges. Grounding provisions provided.

Product Details

General

Application	Designed for use in control and instrumentation applications in areas which do not require oil-tight and dust-tight specifications.
Color	Gray
Construction	Seam and Spot Welded
Cover Type	Hinged Cover
Finish Type	Smooth
Knockouts	No
Listings	UL, CSA
Material	Carbon Steel
Mounting Method	Mounting Holes
Type	Enclosure
UPC	786725612222

Dimensions

Actual Depth	6.630 in
Depth	6 in
Height	36 in
Weight	72 lb
Width	30 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• UL• CSA
Nema Rating	NEMA 1
UL Listed	Yes