



N412202208CDSS

by Wiegmann
Catalog ID: N412202208CDSS

N412 Single Door Flanged Disconnect Ultimate Series 20X22X8 304 Stainless Steel

- Bodies and doors are fabricated from 304 stainless steel
- Seams are continuously welded and ground smooth
- Doors are sealed with a poured in place gasket
- Mounting holes are located in the back of the enclosure
- Latching system interlocks with the disconnect handle for added safety

Bodies and doors fabricated from 14 gauge 304 stainless steel. Continuously plasma welded seams. Increased tub opening for better access. Concealed hinges. Easy to remove doors are interchangeable. Grounding provisions included. Doors are sealed with poured-in-place polyurethane gasket. Mounting holes in rear of enclosure. Studs for mounting optional sub panel. Door latching system installed on door with a slotted insert defeater mechanism to open. Latching system interlocks with the disconnect handle for added safety. 2pt latch system.

Product Details

General

Application	These general purpose disconnect enclosures accept major brand disconnect switches and circuit breakers, available with or without Wiegmann-supplied defeater door handle and handle hardware.
Construction	Continuously Welded Seams
Finish Type	Smooth Grained
Latches Type	2-Point
Listings	UL, CSA
Material	304 Stainless Steel
Mounting Method	Mounting Holes
Number of Doors (Fixed)	1
Type	Enclosure

UPC	786725862627
-----	--------------

Dimensions

Cubic Capacity	3520 cu.in
Depth	8 in
Height	20 in
Weight	43 lb
Width	22 in

Certifications and Compliance

Certified Listed	<ul style="list-style-type: none">• CSA• IEC• UL
Nema Rating	4
UL Listed	Yes