



N412242410CGP

by Wiegmann
Catalog ID: N412242410CGP

N412 Single Door Ultimate with Gland Plate 24X24X10 Carbon Steel - Gray

Product Details

General

Application	For use where dirt, dust, oil, water and other contaminants are present. Typical applications include municipal infrastructure, water treatment plants and other industrial or commercial facilities.
Color	Gray
Material	Carbon Steel
Mounting Type	Wall Mount
Number of Doors (Fixed)	1
Series	Ultimate
UPC	786725890699

Dimensions

Cubic Capacity	5760 cu.in
Depth	10 in
Height	24 in
Weight	58 lb
Width	24 in

Certifications and Compliance

Certified Listed	cULus
Nema Rating	NEMA 4