

NA350-6

by CMC
Catalog ID: NA350-6

- Dual-Rated For Aluminum or Copper Conductors, CO-OX oxide inhibitor is omitted
- Clear plated for low-contact resistance
 - Fully tested to ANSI C119.4 for Class ‘A’ connectors
 - Supplied with radial-tipped set-screws
 - 105 ° C rated black plastisol cover available
 - Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
 - Includes CO-OX oxide inhibitor in all conductor holes
 - Each unit individually wrapped and labeled for ease of identification and cleanliness
 - For installation, CMC® recommends the use of a 9” insulated Allen wrench



Product Details

General

Material	Aluminum
UPC	192663069781

Dimensions

Height	1.25 in
Length	5.61 in
Width	1 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	350 Kcmil - #12 AWG
-----------------	---------------------



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

