



# NA750-4

by CMC  
Catalog ID: NA750-4



- Dual-Rated For Aluminum or Copper Conductors, CO-OX oxide inhibitor is omitted
- Clear plated for low-contact resistance
  - Fully tested to ANSI C119.4 for Class ‘A’ connectors
  - Supplied with radial-tipped set-screws
  - 105 ° C rated black plastisol cover available
  - Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
  - Includes CO-OX oxide inhibitor in all conductor holes
  - Each unit individually wrapped and labeled for ease of identification and cleanliness
  - For installation, CMC® recommends the use of a 9” insulated Allen wrench

## Product Details

### General

Material	Aluminum
UPC	192663070053

### Dimensions

Height	1.88 in
Length	5.49 in
Width	1.38 in

### Electrical Ratings

Voltage Rating	600 V
----------------	-------

### Conductor Related

Conductor Range	750 Kcmil - #2 AWG
-----------------	--------------------



**CONNECTOR MANUFACTURING COMPANY**  
3501 Symmes Road  
Hamilton, Ohio 45015 - 1369  
513 - 860 - 4455(Press 2 for Customer Service and Sales)  
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

