



NACC250-2SI

by CMC

Catalog ID: NACC250-2SI

Dual-Rated For Aluminum or Copper Conductors

- Clear plated for low-contact resistance
- Fully tested to ANSI C119.4 for Class 'A' connectors
- Supplied with radial-tipped set-screws
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Includes CO-OX oxide inhibitor in all conductor holes
- Each unit is individually wrapped and labeled for ease of identification and cleanliness
- For installation, CMC® recommends the use of a 9" insulated Allen wrench

Product Details

General

Material	Aluminum
UPC	192663088102

Dimensions

Height	2.13 in
Length	2 in
Width	2.06 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	250 Kcmil - #12 AWG
-----------------	---------------------

Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - UL Recognized	Yes
RUS Listed Reference	Yes



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

