



# NACC350-2SI

by CMC

Catalog ID: NACC350-2SI

Dual-Rated For Aluminum or Copper Conductors

- Clear plated for low-contact resistance
- Fully tested to ANSI C119.4 for Class 'A' connectors
- Supplied with radial-tipped set-screws
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Includes CO-OX oxide inhibitor in all conductor holes
- Each unit is individually wrapped and labeled for ease of identification and cleanliness
- For installation, CMC® recommends the use of a 9" insulated Allen wrench

## Product Details

### General

Material	Aluminum
UPC	192663081240

### Dimensions

Height	2.31 in
Length	2.2 in
Width	2.5 in

### Electrical Ratings

Voltage Rating	600 V
----------------	-------

### Conductor Related

Conductor Range	350 Kcmil - #12 AWG
-----------------	---------------------

### Certifications and Compliance

Certification - CSA Approved	Yes
------------------------------	-----

Certification - UL Recognized	Yes
RUS Listed Reference	Yes



**CONNECTOR MANUFACTURING COMPANY**  
3501 Symmes Road  
Hamilton, Ohio 45015 - 1369  
513 - 860 - 4455(Press 2 for Customer Service and Sales)  
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

