

# NACC4-5S

by CMC  
Catalog ID: NACC4-5S



Dual-Rated For Aluminum or Copper Conductors

- CMC® Flex tap is available in two through eight conductor configurations in five conductor sizes
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Connector is encapsulated in clear PVC rated at 240 volts per mil
- Clear cover allows visual inspection of conductors during installation
- Fully tested to ANSI C119.4 for Class ‘A’ connectors

## Product Details

### General

Material	Aluminum
UPC	192663088294

### Dimensions

Height	1.12 in
Length	3 in
Width	1.06 in

### Electrical Ratings

Voltage Rating	600 V
----------------	-------

### Conductor Related

Conductor Range	#4 AWG to #14 AWG
-----------------	-------------------

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Recognized	Yes

RUS Listed Reference	No
----------------------	----



**CONNECTOR MANUFACTURING COMPANY**

3501 Symmes Road  
Hamilton, Ohio 45015 - 1369  
513 - 860 - 4455(Press 2 for Customer Service and Sales)  
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

