



NACC600-8SI

by CMC
Catalog ID: NACC600-8SI

Dual-Rated For Aluminum or Copper Conductors

- Clear plated for low-contact resistance
- Fully tested to ANSI C119.4 for Class ‘A’ connectors
- Supplied with radial-tipped set-screws
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Includes CO-OX oxide inhibitor in all conductor holes
- Each unit is individually wrapped and labeled for ease of identification and cleanliness
- For installation, CMC® recommends the use of a 9” insulated Allen wrench

Product Details

General

Material	Aluminum
UPC	192663081776

Dimensions

Height	2.75 in
Length	10.4 in
Width	2.5 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	600 Kcmil - #4 AWG
-----------------	--------------------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Recognized	Yes

RUS Listed Reference

Yes



CONNECTOR MANUFACTURING COMPANY

3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

