

# NNM750-3I

by CMC

Catalog ID: NNM750-3I



Nema mounting transformer connectors

- Clear plated for low-contact resistance.
- Fully tested to ANSI C119.4 for Class 'A' connectors
- Supplied with aluminum radial-tipped setscrews Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Includes CO-OX oxide inhibitor in all conductor holes
- Each unit individually wrapped and labeled for ease of identification and cleanliness
- For installation, CMC® recommends the use of a 9" insulated Allen wrench
- A torque wrench should be used to ensure the proper torque is achieved

## Product Details

### Dimensions

Height	1.75 in
Length	7.28 in
Width	1.38 in

### Conductor Related

Conductor Range	750 Kcmil - #2 AWG
-----------------	--------------------