



NP2416G

by Wiegmann
Catalog ID: NP2416G

Back Panel (N1/3R/4/12) 21X13 Carbon Steel - Galvanized

The NP Series back panels are used in large, wall-mount enclosures including the N1, RHC, N4, N4X, and N412, allowing the user to mount many types of electrical components.

- Fabricated from pre-galvanized steel
- Panels mount to provided collar studs

Galvanized panels are 12 gauge. Panel with any side over 20.00" has 3/4" flange on all sides. Optional "G" panels have a conductive finish (no paint). Panels fit the following enclosures: NEMA 1, Large (NIC); NEMA 3R, hinged Cover (RHC, Large); NEMA 4, 412, & 4X Single Door (N12, N4, N412, SSN4, SSN43PT, SSN43PTW); NEMA 12, 2-Door Wall-Mount (WAWF), Single Door; Right Flange Disconnect (SDN12, ABM12); Large JIC (B-CH, Large) Single door N12.

Product Details

General

Application	For use with NEMA 1, 3R, 12, 4, and 4X wall-mounts.
Construction	Flanged
Finish Type	Galvanized
Material	Carbon Steel
Mounting Method	Mounting Holes
Series	NP
Type	Back Panel
UPC	786725867004

Dimensions

Actual Height	1.375 in
Actual Width	23.25 in
Height	1 in
Weight	5 lb
Width	23 in