



NP4236PP

by Wiegmann
Catalog ID: NP4236PP

Perforated Panel (N1/3R/4/12) 39X33 Carbon Steel - White

The NP Series perforated back panels are used in large, wall-mount enclosures including the N1, RHC, N4, N4X, and N412, allowing the user to mount many types of electrical components.

- Fabricated from carbon steel
- Painted with white polyester powder
- Perforated panels accept self-tapping screws which eliminates the need to measure, mark, and drill when mounting components

Perforated panels are fabricated from 14 gauge. Panel with any side over 20.00" has 3/4" flange on all sides. Panels fit the following enclosures: NEMA 1, Large (NIC); NEMA 3R, hinged Cover (RHC, Large); NEMA 4, 412, & 4X Single Door (N12, N4, N412, SSN4, SSN43PT, SSN43PTW); NEMA 12, 2-Door Wall-Mount (WAWF), Single Door; Right Flange Disconnect (SDN12, ABM12); Large JIC (B-CH, Large) Single door N12.

Product Details

General

Application	For use with NEMA 1, 3R, 12, 4, and 4X wall-mounts.
Color	White
Construction	Flanged
Finish Type	Smooth hybrid paint
Material	Carbon Steel
Mounting Method	Mounting Holes
Series	NP
Type	Back Panel
UPC	786725866359

Dimensions

Actual Height	1.375 in
Actual Width	33.25 in
Height	1 in
Weight	44 lb
Width	33 in