



NPB3-350I

by CMC

Catalog ID: NPB3-350I

Transformer eyebolt connectors, blind hole wire port

- For moisture resistance, conductor ports are not drilled through the body
- Clear plated for low-contact resistance
- For installation on equipment secondary adaptors
- Stud is electro-tin plated
- Supplied with aluminum radial-tipped set-screws
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Includes CO-OX oxide inhibitor in all conductor holes
- Each unit individually wrapped and labeled for ease of identification and cleanliness
- For installation, CMC® recommends the use of a 9" insulated Allen wrench

Product Details

General

Type	Adapters
------	----------

Dimensions

Height	1.375 in
Length	3.99 in
Width	1.59 in

Conductor Related

Conductor Range	350 Kcmil-2 AWG
-----------------	-----------------