

# NPB4-350I

by CMC  
Catalog ID: NPB4-350I



Transformer eyebolt connectors, blind hole wire port, dual-rated connectors for aluminum or copper conductors

- For moisture resistance, conductor ports are not drilled through the body.
- Clear plated for low-contact resistance.
- Fully tested to ANSI C119.4 for Class 'A' connectors.
- For installation on equipment secondary adaptors.
- Stud is electro-tin plated.
- Supplied with aluminum radial-tipped set-screws.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Includes CO-OX oxide inhibitor in all conductor holes.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9" insulated Allen wrench.

## Product Details

### General

Material	Aluminum Alloy, 6061-T6
Type	Adapters
UPC	192663080281

### Dimensions

Diameter - Stud	0.5 in
Height	1.375 in
Length	5.03 in
Stud Inside Diameter	0.5 in
Width	1.59 in

### Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	350 Kcmil - #12 AWG
Number Of Conductors	4



**CONNECTOR MANUFACTURING COMPANY**  
3501 Symmes Road  
Hamilton, Ohio 45015 - 1369  
513 - 860 - 4455(Press 2 for Customer Service and Sales)  
To email customer Service: [jrex@cmclugs.com](mailto:jrex@cmclugs.com)

