

# NPP3-250I

by CMC  
Catalog ID: NPP3-250I



Transformer eyebolt connectors

- Clear plated for low-contact resistance
- Fully tested to ANSI C119.4 for Class 'A' connectors
- For installation on equipment secondary transformers
- Stud is electro-tin plated
- Supplied with aluminum radial-tipped set-screws
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength
- Includes CO-OX oxide inhibitor in allconductor holes
- Each unit individually wrapped and labeled for ease of identification and cleanliness
- For installation, CMC® recommends the use of a 9" insulated Allen wrench

## Product Details

### General

Type	Adapters
------	----------

### Dimensions

Height	1.13 in
Length	3.64 in
Width	0.88 in

### Conductor Related

Conductor Range	250 Kcmil - #12 AWG
-----------------	---------------------