

NSA350-6I

by CMC
Catalog ID: NSA350-6I



- Stud-mount transformer connectors, uni-joint, Dual rated connectors for Aluminum or Copper conductors
- Clear plated for low-contact resistance.
 - Fully tested to ANSI C119.4 for Class ‘A’ connectors.
 - Supplied with aluminum radial-tipped set-screws.
 - Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
 - Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole.
 - Each unit individually wrapped and labeled for ease of identification and cleanliness.
 - For installation, CMC® recommends the use of a 9” insulated Allen wrench.
 - A torque wrench should be used to ensure the proper torque is achieved.

Product Details

General

Material	Aluminum Alloy, 6061-T6
UPC	192663074655

Dimensions

Height	1.38 in
Length	8.06 in
Width	1 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	350 Kcmil - #12 AWG
Number Of Conductors	6



CONNECTOR MANUFACTURING COMPANY
3501 Symmes Road
Hamilton, Ohio 45015 - 1369
513 - 860 - 4455(Press 2 for Customer Service and Sales)
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

