

# NSC250-6

by CMC  
Catalog ID: NSC250-6



Stud-mount transformer connectors, allows left or right-hand mounting, Dual rated connectors for Aluminum or Copper conductors, Insulated Stud-Mount Connectors, CO-OX Oxide inhibitor is omitted

- Injection-molded clear plastic cover insulating a NSSM or NSM connector.
- Injection-molded black rubber cover (NSSR/NSR series) available upon request. Consult factory for availability and minimum order quantities.
- Fully tested to ANSI C119.4 for Class ‘A’ connectors.
- Offers fast, economical, reusable, dependable connections for right or left-hand installations.
- Supplied with radial-tipped set-screws.
- Clear plated for low-contact resistance.
- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole.
- Each unit individually wrapped and labeled for ease of identification and cleanliness.
- For installation, CMC® recommends the use of a 9” insulated Allen wrench.
- A torque wrench should be used to ensure the proper torque is achieved.

## Product Details

### General

|          |                         |
|----------|-------------------------|
| Material | Aluminum Alloy, 6061-T6 |
|----------|-------------------------|

### Dimensions

|        |         |
|--------|---------|
| Height | 3.17 in |
| Length | 8.77 in |
| Width  | 3.17 in |

### Conductor Related

|                      |                     |
|----------------------|---------------------|
| Conductor Range      | 250 Kcmil - #12 AWG |
| Number Of Conductors | 6                   |



**CONNECTOR MANUFACTURING COMPANY**

3501 Symmes Road  
Hamilton, Ohio 45015 - 1369  
513 - 860 - 4455(Press 2 for Customer Service and Sales)  
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

