

NSSM500-6AI

by CMC
Catalog ID: NSSM500-6AI



- Stud-mount transformer connectors, Dual rated connectors for Aluminum or Copper conductors, 5/8-11 In Stud
- NSSM with patented Keyhole mounting.
 - Clear plated for low-contact resistance.
 - Fully tested to ANSI C119.4 for Class ‘A’ connectors.
 - Offers fast, economical, reusable, dependable connections for right or left-hand installations.
 - Supplied with aluminum radial-tipped set-screws.
 - Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
 - 105°C Rated black plastisol cover available.
 - Includes CO-OX oxide inhibitor in all conductor holes and stud-mounting hole.
 - Each unit individually wrapped and labeled for ease of identification and cleanliness.
 - For installation, CMC® recommends the use of a 9” insulated Allen wrench.
 - A torque wrench should be used to ensure the proper torque is achieved.

Product Details

General

Material	Aluminum Alloy, 6061-T6
UPC	192663070848

Dimensions

Height	1.75 in
Length	9.2 in
Width	1.38 in

Electrical Ratings

Voltage Rating	600 V
----------------	-------

Conductor Related

Conductor Range	500 Kcmil - #10 AWG
Number Of Conductors	6