

# NUB500-6I

by CMC

Catalog ID: NUB500-6I



Stud-mount transformer connectors, slip-fit with patented sharkbite™ mount

- Connector fabricated from 6061-T6 aluminum alloy for conductivity and strength.
- Supplied with aluminum radial-tipped set screws.
- Includes inhibitor in all ports and stud-mounting hole.
- Patented two-in-one Sharkbite™ mounting hole feature allows the connector to fit on a 5/8" - 11 or 1" - 14 transformer stud. Both sizes fit in the same hole.
- Sharkbite™ mounting hole feature provides 10 times the surface area contact on the stud over traditional connectors.
- The Sharkbite™ feature also securely locks the connector onto the stud to eliminate wobble when installing the conductors.
- Fully tested to ANSI C119.4 for Class 'A' connectors.

## Product Details

### General

Material	Aluminum Alloy, 6061-T6
UPC	192663085712

### Dimensions

Height	1.75 in
Length	9.2 in
Width	1.38 in

### Electrical Ratings

Voltage Rating	600 V
----------------	-------

### Conductor Related

Conductor Range	500 Kcmil - #10 AWG
-----------------	---------------------



**CONNECTOR MANUFACTURING COMPANY**  
3501 Symmes Road  
Hamilton, Ohio 45015 - 1369  
513 - 860 - 4455(Press 2 for Customer Service and Sales)  
To email customer Service: [jrex @cmclugs.com](mailto:jrex@cmclugs.com)

