



NEVIS

LED Bulkhead

The **Nevis LED** delivers an instant bright white light equivalent to a 70W HPS. Designed for low profile applications, the luminaire can be mounted on walls, handrails and ceilings as a wellglass making it ideal for walkways or restricted height areas.

A side mounted terminal chamber allows for flush mounting and ease of installation. Its excellent temperature range of -50°C to +55°C makes it a global lighting solution providing high quality lighting at extreme temperatures.



UK CE

International Approvals

Mounting Options

Ceiling. Wall. High Bay. Pole/Stanchion. Bulkhead. Wellglass.

Standard Specification

Nevis LED Bulkhead

Enclosure	Aluminium alloy LM6 to BS 1490 (AC44100) All fastenings A4 stainless steel Toughened glass dome cover
Entry	2x M20 cable entries
Termination	3 core 6mm ² max. conductor with looping
Installation	Flush mounting bracket
Control Gear	Electronic Driver
Colour Temperature (CCT)	5650K (Cool White)
Colour Rendering Index (Ra)	>70
Maintenance	Access via hinged front glass cover assembly
Ingress Protection	IP66 to EN 60529
Surge Protection	4kV
Electrical Supply	100-277V AC 50/60 Hz 110-390V DC

Features

- ◆ Highly **Energy Efficient**
- ◆ **Compact** construction
- ◆ **Lower power consumption** than HID lamps
- ◆ Low temperature applications **to -55°C**
- ◆ **60,000 maintenance free hours** 70% initial lumens

Std. Cat No.	Delivered Output	Power Consumption	Ambient °C	Weight
NEVI/052/LE	4058 lm	48W	-55 to +55	12.5kg

Options - Suffix to Catalogue No.

/M25	M25 Cable entries	/P	Marine grade polyester paint coating (RAL 7043)
		/3-4NPT	3/4" NPT entries

Accessories *Accessories should be ordered separately*

	Order Code
Pole mounting bracket assembly (38-50mm diameter poles)	SNEV1-0001
Wire Guard	SNEV1-0002
Hand rail mounting bracket assembly	SNEV4-0003

