

PDV-100 Optima Arrester (5.1 kV  
MCOV, 7333 Hardware)

By OHIO BRASS  
Catalog # [2137057333](#)

IEEE Heavy Duty / IEC Distribution High Polymer Housed Surge  
Arrester



\*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	Transformer Bracket
Cantilever Bending Strength - Max.	80 Nm
Catalog Number	2137057333
Color	Gray Housing
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359612865

Dimensions

Height	3.8 in
Stud Type	3/8-16

Electrical Ratings

Creep and Leakage Distance	11.3 in (287 mm)
Current - Low Current Long Duration (LCLD) Test	250 A
Duty Cycle	6 kV
Frequency Rating	48-62 Hz
MCOV	5.1 kV

Maximum .5 Microsecond Discharge Volts @ Classifying Current	22.4 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"><li>• 16 kV @ 1.5 kA</li><li>• 17.1 kV @ 3 kA</li><li>• 18.2 kV @ 5 kA</li><li>• 19.8 kV @ 10 kA</li><li>• 22.5 kV @ 20 kA</li><li>• 26.5 kV @ 40 kA</li></ul>
Maximum Switching Surge Protective Level @ 500A	14.7 kV
Minimum Strike	4.6 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 Qs

Logistics

Pallet Quantity	128
-----------------	-----

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)  
[Catalogs - Arresters IEEE & IEC Distribution Class](#)  
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese](#)  
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions](#)  
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish](#)  
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French](#)  
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)  
[Literature - Lightning Surge Arresters](#)  
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)  
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)  
[Specifications - Specification for IEEE Heavy Duty Class Distribution Arresters](#)  
[Specifications - 2137057333](#)  
[Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
OB-2137057333-SPEC-EN | REV 3/2025