

**PDV-100 Optima Arrester (17 kV
MCOV, 7324 Hardware)**

By OHIO BRASS
Catalog # [2137177324](#)

IEEE Heavy Duty / IEC Distribution High Polymer Housed Surge
Arrester

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	NEMA 4x5 Crossarm Bracket
Cantilever Bending Strength - Max.	80 Nm
Catalog Number	2137177324
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359414223

Dimensions

Dimensions	13.063 in x 8.313 in x 5.125 in
Height	5.125 in
Length	13.063 in
Minimum Mounting Spacing on Center (Sea Level) - Phase to	8.0 in (203.2 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to	10.0 in (254 mm)
Phase	
Stud Type	3/8-16
Weight	7.3 lb
Width	8.313 in

Electrical Ratings



*Representative Image

Creep and Leakage Distance	28.1 in (713 mm)
Current - Low Current Long Duration (LCLD) Test	250 A
Duty Cycle	21 kV
Frequency Rating	48-62 Hz
MCOV	17 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	71 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 51.4 kV @ 1.5 kA• 55 kV @ 3 kA• 58.2 kV @ 5 kA• 63.5 kV @ 10 kA• 72.1 kV @ 20 kA• 85 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	47 kV
Minimum Strike	9.7 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 Qs

Certifications And Compliance

Buy America(n) Qualified	<ul style="list-style-type: none">• BABA Compliant (All status valid till December 2024)• TAA Compliant (All status valid till December 2024)
--------------------------	--

Logistics

Pallet Quantity	112
-----------------	-----

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)
[Catalogs - Arresters IEEE & IEC Distribution Class](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French](#)

ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.
Literature - Lightning Surge Arresters
Literature - Application Guide: Metal-oxide Surge Arresters for
use on AC systems
Literature - Hubbell Arrester and Wildlife Guard Solution Kits

Sales Drawings - 2137177324 (Reference Only)
Specifications - 2137177324
Specifications - Specification for IEEE Heavy Duty Class
Distribution Arresters
Video - Hubbell Power Systems Metal Oxide Varistor



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
OB-2137177324-SPEC-EN | REV 3/2025