## HUBBELL Power Systems

# PDV-100 Optima Arrester (24.4 kV MCOV, 7324 Hardware)

By OHIO BRASS Catalog # 2137247324

IEEE Heavy Duty / IEC Distribution High Polymer Housed Surge Arrester



#### \*Representative Image

#### **Features**

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP<sup>TM</sup> housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnector operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- · Arresters assembled in Aiken, South Carolina
- 100% routine tested

#### **Application**

Distribution

#### General

Bracket Type NEMA 4x5 Crossarm Bracket

Cantilever Bending Strength - 80 Nm

Max.

Catalog Number 2137247324
Color Gray Housing

EU RoHS Indicator Contact Manufacturer

Material ESP™ Polymer Housing

Mounting Position Upright
Type Distribution
UPC 096359414810

#### **Dimensions**

Height 13.1 in

Minimum Mounting Spacing on 12.0 in (304.8 mm)

Center (Sea Level) - Phase to

Minimum Mounting Spacing on 14.0 in (355.6 mm)

Center (Sea Level)- Phase to

Phase

Stud Type 3/8-16

#### **Electrical Ratings**

Creep and Leakage Distance 42.5 in (1079 mm)

Current - Low Current Long 250 A

Duration (LCLD) Test

Duty Cycle 30 kV
Frequency Rating 48-62 Hz
MCOV 24.4 kV
Maximum .5 Microsecond 105.2 kV

Current

Maximum Discharge Voltage • 76 kV @ 1.5 kA

81.4 kV @ 3 kA
86.2 kV @ 5 kA
94 kV @ 10 kA
106.8 kV @ 20 kA

• 106.8 kV @ 20 kA • 125.9 kV @ 40 kA

69.6 kV

Maximum Switching Surge Protective Level @ 500A

Discharge Volts @ Classifying

Minimum Strike 14 in Pressure Relief Capability- 20

Symmetrical rms (kA)

Time - Low Current Long 2000 Qs

Duration (LCLD) Test

#### **Certifications And Compliance**

Buy America(n) Qualified TAA Compliant (All status valid

till December 2024)

### Logistics

Pallet Quantity 35

#### **Product Assets**

Brochures - Ohio Brass Sets the Standards for Arresters

Catalogs - Arresters IEEE & IEC Distribution Class

Installation Manuals - Installation Instructions for PDV/PVR

Arresters - Chinese

Installation Manuals - PDV-PVR Polymer Distribution Class

Arrester Installation Instructions

Installation Manuals - Installation Instructions for PDV/PVR

Arresters - Spanish

Installation Manuals - Installation Instructions for PDV/PVR

Arresters - French

ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.

Literature - Lightning Surge Arresters

Literature - Application Guide: Metal-oxide Surge Arresters for

use on AC systems

Literature - Hubbell Arrester and Wildlife Guard Solution Kits



©2025 Hubbell Incorporated. All rights reserved OB-2137247324-SPEC-EN | REV 3/2025