

**PDV-100 Optima Arrester (29 kV  
MCOV, 7314 Hardware)**

By OHIO BRASS  
Catalog # [2137297314](#)

IEEE Heavy Duty / IEC Distribution High Polymer Housed Surge  
Arrester



\*Representative Image

**Features**

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

**Application**

Distribution

**General**

Bracket Type	None
Cantilever Bending Strength - Max.	80 Nm
Catalog Number	2137297314
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359401438

**Dimensions**

Height	15.5 in
Minimum Mounting Spacing on Center (Sea Level) - Phase to	14.5 in (368.3 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to	16.5 in (419.1 mm)
Phase	
Stud Type	3/8-16

**Electrical Ratings**

Creep and Leakage Distance	50.4 in (1280 mm)
Current - Low Current Long	250 A
Duration (LCLD) Test	

Duty Cycle	36 kV
Frequency Rating	48-62 Hz
MCOV	29 kV
Maximum .5 Microsecond	126.3 kV
Discharge Volts @ Classifying Current	
Maximum Discharge Voltage	<ul style="list-style-type: none"><li>• 91.3 kV @ 1.5 kA</li><li>• 97.8 kV @ 3 kA</li><li>• 103.5 kV @ 5 kA</li><li>• 112.9 kV @ 10 kA</li><li>• 128.3 kV @ 20 kA</li><li>• 151.2 kV @ 40 kA</li></ul>
Maximum Switching Surge	83.5 kV
Protective Level @ 500A	
Minimum Strike	16.2 in
Pressure Relief Capability- Symmetrical rms (kA)	20
Time - Low Current Long	2000 Qs
Duration (LCLD) Test	

**Certifications And Compliance**

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

**Logistics**

Pallet Quantity	35
-----------------	----

**Product Assets**

[Brochures - Ohio Brass Sets the Standards for Arresters](#)  
[Catalogs - Arresters IEEE & IEC Distribution Class](#)  
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese](#)  
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions](#)  
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish](#)  
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French](#)  
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)  
[Literature - Lightning Surge Arresters](#)  
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)  
[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)



A Hubbell brand