

# HUBBELL Power Systems

## PVR Optima (15.3 kV MCOV, 7534 Hardware)

By OHIO BRASS  
Catalog # [2216157534](#)

IEEE Riser Pole Class Polymer Housed Surge Arrester



### Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

### General

Application	Distribution
Bracket Type	Transformer Bracket
Cantilever Bending Strength - Max.	135 Nm
Color	Gray Housing
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution

### Dimensions

Height	12.4 in
Stud Type	3/8-16

### Electrical Ratings

Creep and Leakage Distance	26 in (660 mm)
Current - Low Current Long	250 A
Duration (LCLD) Test	
Duty Cycle	18 kV
Frequency Rating	48-62 Hz
MCOV	15.3 kV
Maximum .5 Microsecond	54.5 kV
Discharge Volts @ Classifying Current	
Maximum Discharge Voltage	41.8 kV @ 1.5 kA
	43.6 kV @ 3 kA
	45.4 kV @ 5 kA
	48.9 kV @ 10 kA
	54 kV @ 20 kA
	62.6 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	36 kV
Minimum Strike	9.7 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long	2000 Qs
Duration (LCLD) Test	

## Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)

[Catalogs - Arresters IEEE & IEC Distribution Class](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - Spanish](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - Chinese](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - French](#)

[Installation Manuals - PDV-PVR Polymer Distribution Class](#)

[Arrester Installation Instructions](#)

[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc.](#)

[Effective 2020-2023, Multi-site \(English\)](#)

[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)

[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)

[Literature - Lightning Surge Arresters](#)

[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)

[Video - Hubbell Power Systems Metal Oxide Varistor](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
OB-2216157534-SPEC-EN | REV 6/2024