

HUBBELL Power Systems

PVR Optima (22 kV MCOV, 7214 Hardware)

By OHIO BRASS
Catalog # [2216227214](#)

IEEE Riser Pole Class Polymer Housed Surge Arrester



*Representative Image

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Application	Distribution
Bracket Type	None
Cantilever Bending Strength - Max.	135 Nm
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359418641

Dimensions

Dimensions	13.063 in x 8.313 in x 5.125 in
Height	5.125 in
Length	13.063 in
Minimum Mounting Spacing on Center (Sea Level) - Phase to	10.5 in (266.7 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to Phase	12.5 in (317.5 mm)
Stud Type	3/8-16
Weight	4.4 lb
Width	8.313 in

Electrical Ratings

Creep and Leakage Distance	52 in (1321 mm)
Current - Low Current Long	250 A
Duration (LCLD) Test	
Duty Cycle	27 kV
Frequency Rating	48-62 Hz
MCOV	22 kV
Maximum .5 Microsecond	81.4 kV
Discharge Volts @ Classifying Current	
Maximum Discharge Voltage	61.6 kV @ 1.5 kA
	64.2 kV @ 3 kA
	66.8 kV @ 5 kA
	72 kV @ 10 kA
	79.6 kV @ 20 kA
	92.2 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	53 kV
Minimum Strike	18 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long	2000 Qs
Duration (LCLD) Test	
Withstand Voltage - 60 Hz Wet	58
Withstand Voltage - Lightning Impulse	136.6

Logistics

Pallet Quantity	35
-----------------	----

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)

[Catalogs - Arresters IEEE & IEC Distribution Class](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - Spanish](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - Chinese](#)

[Installation Manuals - Installation Instructions for PDV/PVR](#)

[Arresters - French](#)

[Installation Manuals - PDV-PVR Polymer Distribution Class](#)

[Arrester Installation Instructions](#)

[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc.](#)

[Effective 2020-2023, Multi-site \(English\)](#)

[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)

[Literature - Hubbell Arrester and Wildlife Guard Solution Kits](#)

[Literature - Lightning Surge Arresters](#)

[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)

[Sales Drawings - 2216227214 \(Reference Only\)](#)

[Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand