

PVR Optima (24.4 kV MCOV, 7314 Hardware)

By OHIO BRASS
Catalog # [2216247314](#)



IEEE Riser Pole Class Polymer Housed Surge Arrester

Features

- Over 35 years of excellent field performance with over 40 million distribution arresters installed
- Long lasting ESP™ housing material with superior mechanical strength and electrical characteristics
- Reliable capacitive disconnecter operates at fault currents as low as 1 Amp
- Dynamic triple sealing system protects internal components from moisture ingress to extend service lifetime
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

Application

Distribution

General

Bracket Type	None
Cantilever Bending Strength - Max.	135 Nm
Catalog Number	2216247314
Color	Gray Housing
EU RoHS Indicator	Contact Manufacturer
Material	ESP™ Polymer Housing
Mounting Position	Upright
Type	Distribution
UPC	096359418832

Dimensions

Dimensions	0.001 in x 0.001 in x 15.3 in
Height	15.3 in
Length	0.001 in
Minimum Mounting Spacing on Center (Sea Level) - Phase to	11.5 in (292.1 mm)
Minimum Mounting Spacing on Center (Sea Level)- Phase to Phase	13.5 in (342.9 mm)
Stud Type	3/8-16
Weight	4.6 lb
Width	0.001 in

Electrical Ratings

Creep and Leakage Distance	49 in (1245 mm)
Current - Low Current Long Duration (LCLD) Test	250 A
Duty Cycle	30 kV
Frequency Rating	48-62 Hz
MCOV	24.4 kV
Maximum .5 Microsecond Discharge Volts @ Classifying Current	91 kV
Maximum Discharge Voltage	<ul style="list-style-type: none"> • 69.3 kV @ 1.5 kA • 72.2 kV @ 3 kA • 75.2 kV @ 5 kA • 81 kV @ 10 kA • 89.5 kV @ 20 kA • 103.7 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	59.6 kV
Minimum Strike	18 in
Pressure Relief Capability-Symmetrical rms (kA)	20
Time - Low Current Long Duration (LCLD) Test	2000 Qs
Withstand Voltage - 60 Hz Wet	64.3
Withstand Voltage - Lightning Impulse	150.2

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	35
-----------------	----

Product Assets

[Brochures - Ohio Brass Sets the Standards for Arresters](#)
[Catalogs - Arresters IEEE & IEC Distribution Class](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Chinese](#)
[Installation Manuals - PDV-PVR Polymer Distribution Class Arrester Installation Instructions](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - Spanish](#)
[Installation Manuals - Installation Instructions for PDV/PVR Arresters - French](#)

ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.
Literature - Lightning Surge Arresters
Literature - Application Guide: Metal-oxide Surge Arresters for
use on AC systems

Literature - Hubbell Arrester and Wildlife Guard Solution Kits
Sales Drawings - 2216247314 (Reference Only)
Specifications - 2216247314
Video - Hubbell Power Systems Metal Oxide Varistor



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
OB-2216247314-SPEC-EN | REV 1/2025