

Veri*Lite Line Post Insulator SR 15 kV

By OHIO BRASS
Catalog # 80S0150100

Horizontal Line Post 15 kV Clamptop / Gain Base.



Features

- Weathersheds molded with proprietary silicone rubber
- Proven direct bond interface

Application

Horizontal Line Post

General

Cantilever Bending Strength - Max. 2800 Lbs. (12.5 kN)

Cantilever Bending Strength - Routine 1235 Lbs. (5.5 kN)

EU RoHS Indicator Contact Manufacturer

Fitting - Ground/Base Gain Base

Fitting - Live Line End Horizontal Clamptop

Material Silicone

Material - End Fitting Galvanized Steel

Number of Sheds 2

Tension Range 2500 lb

UPC 096359438434

Dimensions

| | |
|---------------------|-------------------------|
| Angle | 5 |
| Diameter - Shed(s) | 4.8" (121mm) |
| Dimensions | 15 in x 4.77 in x 12 in |
| Height | 12 in |
| Length | 15 in |
| Length - Effective | 12.5 in |
| Rod Diameter | 1.5 in |
| Thickness - Housing | 0.22" (5.5mm) |
| Weight | 9.8 lb |
| Width | 4.77 in |

Electrical Ratings

| | |
|--|---------------|
| Arc Distance - Dry | 7.4" (188mm) |
| Creep and Leakage Distance | 11.0" (279mm) |
| Critical Impulse Flashover (CIFO) - Positive | 150 kV |
| Flashover Voltage - 60 Hz Dry | 90 kV |
| Flashover Voltage - 60 Hz Wet | 70 kV |
| Voltage - Line | 15000 V |
| Voltage Rating | 15 kV |
| Withstand Voltage - Lightning Impulse (Positive) | 140 kV |

Certifications and Compliance

| | |
|----------------------|------|
| Industry Standard(s) | ANSI |
|----------------------|------|

Logistics

| | |
|------------------|----|
| Carton Quantity | 2 |
| Pallet Quantity | 40 |
| Standard Package | 3 |

Product Assets

[Catalogs - Veri*Lite Line Post Insulators Catalog \(CA08051E\)](#)
[Sales Drawings - Veri Lite 15 KV Line Post \(80S015-0100\) \(Reference Only\)](#)