

**Veri\*Lite Line Post Insulator SR 15  
kV**

By OHIO BRASS  
Catalog # [80S0150109](#)

Horizontal Line Post 15 kV Clamptop / Stud Base 3/4"-10 Tap.



**Features**

- Weathersheds molded with proprietary silicone rubber
- Proven direct bond interface

**Application**

Horizontal Line Post

**General**

Cantilever Bending Strength - Max.	2800 Lbs (12.5 kN)
Cantilever Bending Strength - Routine	1235 Lbs. (5.5 kN)
EU RoHS Indicator	Contact Manufacturer
Fitting - Ground/Base	3/4" Stud Base
Fitting - Live Line End	Horizontal Clamptop
Material	Silicone
Material - End Fitting	Galvanized Steel
Number of Sheds	2
Tension Range	2500 lb
UPC	096359438441

**Dimensions**

Diameter - Shed(s)	4.8" (121mm)
Length - Effective	13.3 in
Rod Diameter	1.5 in
Thickness - Housing	0.22" (5.5mm)
Weight	6.9 lb

**Electrical Ratings**

Arc Distance - Dry	7.4" (188mm)
Creep and Leakage Distance	11.0" (279mm)
Critical Impulse Flashover (CIFO) - Positive	150 kV
Flashover Voltage - 60 Hz Dry	90 kV
Flashover Voltage - 60 Hz Wet	70 kV
Voltage - Line	15000 V
Voltage Rating	15 kV
Withstand Voltage - Lightning Impulse (Positive)	140 kV

**Certifications and Compliance**

Industry Standard(s)	ANSI
----------------------	------

**Logistics**

Carton Quantity	3
Pallet Quantity	60
Standard Package	3

**Product Assets**

[Catalogs - Veri\\*Lite Line Post Insulators Catalog \(CA08051E\)](#)  
[Sales Drawings - Veri Lite 15 KV Line Post \(80S015-0109\)](#)  
(Reference Only)