

HUBBELL Power Systems

Veri*Lite Line Post Insulator SR 15 kV

By OHIO BRASS
Catalog # [80S0150F09](#)

Vertical Line Post 15 kV F-Neck / Stud Base 3/4"-10 Tap.



Features

- Weathersheds molded with proprietary silicone rubber
- Proven direct bond interface

General

Application	Vertical Line Post
Cantilever Bending Strength - Max.	2800 Lbs (12.5 kN)
Cantilever Bending Strength - Routine	1235 Lbs. (5.5 kN)
EU RoHS Indicator	Contact Manufacturer
Fitting - Ground/Base	3/4" Stud Base
Fitting - Live Line End	F-Neck
Material	Silicone
Material - End Fitting	Galvanized Steel
Number of Sheds	2
Tension Range	2500 lb
UPC	096359438489

Dimensions

Angle	0
Diameter - Shed(s)	4.8" (121mm)
Length - Effective	12.4 in
Rod Diameter	1.5 in
Thickness - Housing	0.22" (5.5mm)
Weight	6.6 lb

Electrical Ratings

Arc Distance - Dry	7.4" (188mm)
Creep and Leakage Distance	11.0" (279mm)
Critical Impulse Flashover (CIFO) - Positive	150 kV
Flashover Voltage - 60 Hz Dry	90 kV
Flashover Voltage - 60 Hz Wet	70 kV
Voltage - Line	15000 V
Voltage Rating	15 kV
Withstand Voltage - Lightning Impulse (Positive)	140 kV

Certifications And Compliance

Industry Standard(s)	ANSI
----------------------	------

Logistics

Carton Quantity	3
Pallet Quantity	60
Standard Package	3

Product Assets

[Catalogs - Veri*Lite Line Post Insulators Catalog](#)
[Sales Drawings - Veri Lite 15 KV Line Post \(Reference Only\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
OB-80S0150F09-SPEC-EN | REV 6/2024