

Veri*Lite Line Post Insulator SR 15 kV

By OHIO BRASS
Catalog # [80S0150K09](#)

Line Post 15 kV Universal Clamp / Stud Base 3/4"-10 Tap.



*Representative Image

Features

- Weathersheds molded with proprietary silicone rubber
- Proven direct bond interface

Application

Universal Clamp

General

| | |
|---------------------------------------|--------------------|
| Cantilever Bending Strength - Max. | 2801 Lbs (12.5 kN) |
| Cantilever Bending Strength - Routine | 1236 Lbs. (5.5 kN) |
| Fitting - Ground/Base | 3/4" Stud Base |
| Fitting - Live Line End | Universal Clamp Al |
| Material | Silicone |
| Material - End Fitting | Aluminum |
| Number of Sheds | 3 |
| Tension Range | 2500 lb |
| UPC | 096359665991 |

Dimensions

| | |
|---------------------|------------------------|
| Diameter - Shed(s) | 4.8" (121mm) |
| Dimensions | 15 in x 5 in x 4.77 in |
| Height | 4.77 in |
| Length | 15 in |
| Length - Effective | 13.0 in |
| Rod Diameter | 1.5 in |
| Thickness - Housing | 0.22" (5.5mm) |
| Weight | 6.9 lb |
| Width | 5 in |

Electrical Ratings

| | |
|--|---------------|
| Arc Distance - Dry | 7.4" (188mm) |
| Creep and Leakage Distance | 11.0" (279mm) |
| Critical Impulse Flashover (CIFO) - Positive | 150 kV |
| Flashover Voltage - 60 Hz Dry | 90 kV |
| Flashover Voltage - 60 Hz Wet | 70 kV |
| Voltage - Line | 15000 V |
| Voltage Rating | 15 kV |
| Withstand Voltage - Lightning Impulse (Positive) | 140 kV |

Certifications and Compliance

| | |
|----------------------|------|
| Industry Standard(s) | ANSI |
|----------------------|------|

Logistics

| | |
|------------------|----|
| Carton Quantity | 3 |
| Pallet Quantity | 60 |
| Standard Package | 4 |

Product Assets

[Catalogs - Veri*Lite Line Post Insulators Catalog \(CA08051E\)](#)
[Sales Drawings - Veri Lite 15 kV Line Post \(80S015-OK09\)](#)
(Reference Only)