

**MH3 Arrester (33 kV Rated, 1116 mm  
Creep Distance, AA Hardware)**

By OHIO BRASS  
Catalog # [MH3036GM033AA](#)

IEC Station Medium / Porcelain Housed Surge Arrester

**Features**

- IEC porcelain Station Medium class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

**General**

Catalog Number	MH3036GM033AA
Color	Gray Housing
Material	Porcelain Housing
Type	Station

**Electrical Ratings**

Frequency Rating	48-62 Hz
------------------	----------



Pressure Relief Capability- 63  
Symmetrical rms (kA)

**Certifications And Compliance**

Industry Standard(s) IEC

**Product Assets**

[Catalogs - Station Class Surge Arresters IEEE and IEC](#)  
[Installation Manuals - Porcelain Hollow Core Station Class Arrester Installation Instructions](#)  
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)  
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)  
[Specifications - MH3036GM033AA](#)  
[Specifications - Specification for Hollow Core IEC Station Class Arresters](#)  
[Video - Hubbell Power Systems Metal Oxide Varistor](#)