

MH3 Brrester (60 kV Rated, 2540 mm Creep Distance, BA Hardware)

By OHIO BRASS
Catalog # [MH3072GV060BA](#)

IEC Station Medium / Porcelain Housed Surge Arrester



*Representative Image

Features

- IEC porcelain Station Medium class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Color	Gray Housing
Material	Porcelain Housing
Type	Station

Electrical Ratings

Frequency Rating	48-62 Hz
Pressure Relief Capability-Symmetrical rms (kA)	63

Certifications and Compliance

Industry Standard(s) IEC

Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC \(CA01082E_Catalog 30_0923_web\)](#)
[Installation Manuals - Porcelain Hollow Core Station Class Arrester Installation Instructions \(17-5092\)](#)
[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc. Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)
[Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)