

**MH3 Arrester (120 kV Rated, 3874 mm Creep Distance, AA Hardware)**

By OHIO BRASS  
Catalog # [MH3123BV120AA](#)

IEC Station Medium / Porcelain Housed Surge Arrester

**Features**

- IEC porcelain Station Medium class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

**General**

Catalog Number	MH3123BV120AA
Color	Brown Housing
Material	Porcelain Housing
Type	Station

**Electrical Ratings**

Frequency Rating	48-62 Hz
------------------	----------



Pressure Relief Capability- Symmetrical rms (kA) 63

**Certifications And Compliance**

Industry Standard(s) IEC

**Product Assets**

- [Catalogs - Station Class Surge Arresters IEEE and IEC](#)
- [Installation Manuals - Porcelain Hollow Core Station Class Arrester Installation Instructions](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Specifications - Specification for Hollow Core IEC Station Class Arresters](#)
- [Specifications - MH3123BV120AA](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)