

MH3 Arrester (132 kV Rated, 3874 mm Creep Distance, AA Hardware)

By OHIO BRASS
Catalog # [MH3145GM132AA](#)

IEC Station Medium / Porcelain Housed Surge Arrester

Features

- IEC porcelain Station Medium class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

Catalog Number	MH3145GM132AA
Color	Gray Housing
Material	Porcelain Housing
Type	Station
UPC	096359715559

Electrical Ratings

Frequency Rating	48-62 Hz
------------------	----------



Pressure Relief Capability- 63
Symmetrical rms (kA)

Certifications And Compliance

Industry Standard(s) IEC

Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC](#)
[Installation Manuals - Porcelain Hollow Core Station Class Arrester Installation Instructions](#)
[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
[Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
[Specifications - MH3145GM132AA](#)
[Specifications - Specification for Hollow Core IEC Station Class Arresters](#)
[Video - Hubbell Power Systems Metal Oxide Varistor](#)