

## MH3 Arrester (216 kV Rated, 5747 mm Creep Distance, AA Hardware)

By OHIO BRASS  
Catalog # [MH3245BM216AA](#)

IEC Station Medium / Porcelain Housed Surge Arrester



\*Representative Image

### Features

- IEC porcelain Station Medium class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

### General

Color	Brown Housing
Material	Porcelain Housing
Type	Station

### Electrical Ratings

Frequency Rating	48-62 Hz
Pressure Relief Capability-Symmetrical rms (kA)	63

### Certifications and Compliance

Industry Standard(s) IEC

### Product Assets

[Catalogs - Station Class Surge Arresters IEEE and IEC \(CA01082E\\_Catalog 30\\_0923\\_web\)](#)

[Installation Manuals - Porcelain Hollow Core Station Class Arrester Installation Instructions \(17-5092\)](#)

[ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)

[ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc. Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems \(TD01135E\)](#)

[Video - Hubbell Power Systems Metal Oxide Varistor \(VI01022E0718\)](#)