

HUBBELL

Power Systems

MH3 Arrester (336 kV Rated, 13495 mm Creep Distance, AA Hardware)

By OHIO BRASS
Catalog # [MH3420BV336AA](#)

IEC Station Medium / Porcelain Housed Surge Arrester



Features

- IEC porcelain Station Medium class arrester
- IEEE 693 High Performance Qualification
- High quality MOV discs made in Wadsworth, Ohio since 1978
- Arresters assembled in Aiken, South Carolina
- 100% routine tested

General

| | |
|----------|-------------------|
| Color | Brown Housing |
| Material | Porcelain Housing |
| Type | Station |

Electrical Ratings

| | |
|-----------------------------|----------|
| Frequency Rating | 48-62 Hz |
| Pressure Relief Capability- | 63 |
| Symmetrical rms (kA) | |

Certifications And Compliance

| | |
|----------------------|-----|
| Industry Standard(s) | IEC |
|----------------------|-----|

Product Assets

- [Catalogs - Station Class Surge Arresters IEEE and IEC](#)
- [ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
- [ISO Certificates - ISO 14001:2015 - Hubbell Power Systems Inc.](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)